



You are browsing the product catalog for

United States



LOAD CELLS

# Model 43

Precision Low Profile Load Cell

## Overview



Feedback

Model 43 is a low profile "pancake" type load cells. These bonded foil, strain gage load cells are engineered to measure loads from 5 lb to 500,000 lb. The compression-only Model 43 has a load button which is fixed as an integral part of the load cell and cannot be removed or changed. It provides high performance in non-linearity, hysteresis, and repeatability specifications for such applications as tube mills, extruding processes and weighing. Each unit has a welded construction and can be hermetically sealed for added durability. Model 43 is available with optional 0 Vdc to 5 Vdc or 4 mA to 20 mA output.

### Features

- 0.10 % accuracy
- 5 lb to 500000 lb
- mV/V output (standard); 0 Vdc to 5 Vdc or 4 mA to 20 mA (optional)
- Stainless steel
- Double diaphragm design




Please sign in to view part numbers available for purchase based on your account

Sign In

Search

Part Number	060-0828-02
Description	AL112EL, 1A, 2U, 6B, 15A:MODEL 43, 20, 000 SIGN IN
Part Number	060-J157-01-01
Description	BL320BN, 45X, 92X 49 LBS, PN SIGN IN
Part Number	060-K630-01
Description	CP201HX, 45X 1, 000 TORR ABS. SIGN IN
Part Number	060-P913-01
Description	BP435EJ, 6, 1AC, 2AK, 6A, 7AZ, 10J:MODEL 435, SIGN IN
Part Number	060-R228-01-01
Description	MODEL LFH-7I, 3000 LBS, CUSTOM SIGN IN
Part Number	060-R323-01
Description	MODEL 437, 15, 000 PSIG SIGN IN
Part Number	50092678-001
Description	Ship Torsionmeter - High Shock for HII. SIGN IN

# Product Number



Please sign in to view part numbers available for purchase based on your account

Sign In

060-0828-02  
AL112EL,1A,2U,6B,15A:MODEL 43, 20,000

060-0828-02  
AL112EL,1A,2U,6B,15A:MODEL 43, 20,000

060-J157-01-01  
BL320BN,45X,92X 49 LBS, PN

060-J157-01-01  
BL320BN,45X,92X 49 LBS, PN

060-K630-01  
CP201HX,45X 1,000 TORR ABS.

060-K630-01

CP201HX,45X 1,000 TORR ABS.

060-P913-01

BP435EJ,6,1AC,2AK,6A,7AZ,10J:MODEL 435,

060-P913-01

BP435EJ,6,1AC,2AK,6A,7AZ,10J:MODEL 435,

060-R228-01-01

MODEL LFH-7I, 3000 LBS, CUSTOM

060-R228-01-01

MODEL LFH-7I, 3000 LBS, CUSTOM

060-R323-01

MODEL 437, 15,000 PSIG

060-R323-01

MODEL 437, 15,000 PSIG

50092678-001

Ship Torsionmeter - High Shock for HII.

50092678-001

Ship Torsionmeter - High Shock for HII.

Feedback

**Honeywell**  
**Industrial Automation**  
855 S Mint St  
Charlotte, NC 28202  
800-582-4263

**Product name**  
© Current year Honeywell International Inc.  
All rights reserved.

