

INP1.2-12x34



DESCRIPTION

WHERE TO BUY

RESOURCES

Electrical Specifications:

Max Voc all light levels = 1.9V

200 Lux

- Power: 0.010mW

- Operating Voltage: 0.8V
- Current: 0.012mA
- Average Voc: 1.2V
- Isc: 0.02mA

1000 Lux

- Power: 0.065mW
- Operating Voltage: 1.1V
- Current: 0.059mA
- Average Voc: 1.4V
- Isc: 0.08mA

Physical Specifications:

- Dimensions: 34.0 x 12.0 (mm) / 1.338 x 0.472 (in)
- Weight: 0.004oz / 0.13g
- Thickness: 0.22mm

IV Curve



CONNECT WITH US

NAVIGATION

- Products
- Markets
- Custom Solutions
- Technology
- Education
- Explore

PowerFilm Solar, Inc.
1287 XE Place
Ames, Iowa 50014

515-292-7606
Contact Us

© 2025 PowerFilm Solar, Inc. All rights reserved

[Privacy](#)

[Back to Top](#)