

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF EASE ELECTRONICS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF EASE ELECTRONICS IS PROHIBITED.

REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	30/7/25	CHILLY. L

SPECIFICATIONS:

Current Rating: 3A AC / DC

Withstanding Voltage: 1000V AC/Min.

Temperature Range: - 40 °C ~ +105°C

Insulation Resistance: 1000MΩ Min.

Contact Resistance: 20mΩ Max.





Material:

Base: PA6T UL94V-0, Black

Conductor: Brass / Gold Plated

PH 254 V - 2NP - XX BK X 126
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Category: PH=Pin Header
② Pitch: 254=Pitch 2.54mm
③ Appearance: V= Straight 180°
④ Circuit No.: 204=2*2 PIN.....
⑤ Material: 6T=PA6T UL94V-0
⑥ Color: BK=Black
⑦ Finish: G=Gold Plated
⑧ Option: 126 = Base Width 5.0 / Base Height 2.5 / Bottom Entry 3.0 / Top Entry 6.0



P. C. B LAYOUT

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15 PROJECTION 	APPROVALS	DATE	EASE Ease Electronics Co., Limited Zone A, 2nd Floor, Bldg A, No.45, Qianjin 3rd Rd, Tanzhou, 528467 Zhongshan, Guangdong, China. +86-756-58 8881 0	
	DRAWN BY LUKE. L	29/7/2025	PART NUMBER PH254V-204-6TBKG126	
	CHECKED BY TILY. H	29/7/2025		
	APPROVED BY CHILLY. L	30/7/2025	PRODUCT DESCRIPTION PCB Header, Male, 3A, 250V, Contacts - 4	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		ID I		SERIES NO. PH254
COLOR VARIATIONS MAY OCCUR		DWG. NO. I0622		REV. I
REF		SCALE: NONE		CAD FILE: I0622
				SHEET 1 OF 1