







N=Number.of contacts
Dimension Dim A & Dim B

Dim A	(N-1)×3.81+4.55
Dim B	(N-1)×3.81

Poles	A&B Tolerance
2P-4P	+0.15/-0.15
5P-8P	+0.25/-0.25
9P-16P	+0.30/-0.30
17P-24P	+0.35/-0.35

SIGN	DATE	DESCRIPTION	APPROVER
△			
△			
△			
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item 1 Terminal housing : Thermoplastic (UL 94V-0)
- Item 2 Clamp : Brass ,Ni plated
- Item 3 Wire guard solder pin : Brass ,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 16-24
- Stranded wire(AWG): 16-24
- Torque(Lb-In): 1.7
- Screw: M2
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec

YP xx 21 x 0 A xxx G

No. of poles	0 Black (RAL9005)	000:"@Logo (Standard)
02 2 CONTACTS	2 Red (RAL3001/D)	00A:"ANYTEK"Logo
03 3 CONTACTS	3 Orange(RAL2011/P)	Any special item by
...	4 Yellow(RAL1018/A)	customer request,
24 24 CONTACTS	5 Green(RAL6018/T)	please contact sales
	6 Blue (RAL5015/A)	department.
	8 Grey(RAL7035/D)	

Pb < 40,000ppm
(RoHS)

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YP-3.81mm Series 2P-24P (加高型)				DWG NO.	8YP0201		
PART NO.	YPxx21x0AxxxG				CUST NO.			
APPROVED	CHECKED	DESIGNED	DRAWN					Tolerance
		Aaron 2010.08.23	Aaron 2010.07.20					X. ±0.50
								X.X ±0.30
								X.XX ±0.10
								X° ±1°