


SIGN	DATE	DESCRIPTION	APPROVER
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Note:
● Module female contact, is inserted into the plug housing KV5.08 after crimping the conductor, for conductors from 1.5 to 2.5 mm²

Material data:
● Female contact : PhBz , Tin plated.

Connection data:
● Wire strip length: 7 mm
● Wire range: 1.5~2.5mm²
● Stranded wire(AWG): 14 - 16
● Core diameter including insulation : 2.11 mm ... 3.1 mm

ANYTEK				CUSTOMER COPY			
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD							
TITLE	AR5.08 SERIES AWG 16~14 (1.5~2.5 mm) ²						
PART NO.	AR0000000000G			DWG NO.	8AR0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Kind	Kind		UNIT:	mm	X. ±0.50
		2010.01.06	2009.08.08		SCALE:	2/1	X.X ±0.30
					SHEET:	01/01	X.XX ±0.10
					REV.:	B	X° ±1°