




Pushing Performance
Since 1945

Han 3A-HBM-SL (only f. PCB-adapter)



Part number	09 20 003 0304
Specification	Han 3A-HBM-SL (only f. PCB-adapter)

Identification

Category	Hoods / Housings
Series of hoods/housings	Han A®
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Straight for PCB adapter

Version

Size	3 A
Locking type	Single locking lever
Field of application	Standard Hoods/housings for industrial applications
Pack contents	Please order seal screw separately.

Technical characteristics

Tightening torque	1 Nm Fixing screws M3
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44
	IP65 With seal screw
	IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)



Pushing Performance
Since 1945

Material properties

Material (seal)	NBR
Material (locking)	Steel
Surface (locking)	Zinc plated

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	10
Net weight	20 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140488175
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466