

1

2

3

4

5

6

complete length when assembled app. 42

assembly aid enclosed

SW18
width across
flats: 18

A

B

M12x1




M16x1,5

SW19
width across
flats: 19

pin	colour
1	yellow
2	white
3	orange
4	blue


panel
thickness

Panel cut out
(1:1)



A (2:1)

contact face acc. to
IEC 61076-2-101



recommended torque of counter nut: 2Nm
order contacts separately

cableØ	wire gauge	contact part-no.
4,5-8,8mm	AWG 26-22	09 67 000 5476
	AWG 24-20	09 67 000 8476
	AWG 22-18	09 67 000 3476

	All Dimensions in mm Original Size DIN A4	Scale 1:1	Free size tol.		Ref.
	All rights reserved Department EL PD	Created by 406551	Inspected by farcasiu	Standardisation 14-Feb-2025	Sub.
	Title M12-SD-CC-CRIMP-4P-DCOD-F-STR-SHLD				Date 14-Feb-2025
	Doc-Key / ECM-Nr. DS00204823				State 4.0 - Released
D-32339 Espelkamp			Type TB	Design Number DS00204823	SAP Mat. Number 21038812426
			Rev. G	Page 1/1	