




NOTES:

1. GENERAL SPECIFICATIONS: BIVAR EXTRUDED PROFILE SPECIFICATIONS: BV00-M101.
2. MATERIAL: PVC ALLOY, 94V-0 COMPLIANT, BLACK.
3. TOLERANCE "L" DIMENSION:
0.030 - 0.500 (1.0 - 12.7 mm)±0.005 (0.1mm)
0.505 - 0.750 (12.8 - 19.1 mm)±0.008 (0.2mm)
0.755 - 1.250 (19.2 - 31.8 mm)±0.015 (0.4mm)

REV.	DESCRIPTION	DATE	APPROVED
M	ECO-1258 - MATERIAL COMPLIANCE UPDATE	5/29/2024	D. A.
N	ECO-1341: ADDED ANGLE TOLERANCE	7/25/2025	A.V.



CUSTOMER USE DRAWING

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		BIVAR [®] 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°	 TITLE: EXTRUDED, SELF-RETAINING LED MOUNT	
.XX ± .01			
.XXX ± .005		DRAWING NO: ELM 5-XXX	
DESIGNED: S. IRVING	DATE: 2/3/1998	REVISION: N	
REVISED: K. BARON	DATE: 7/25/2025	SHEET SIZE A	CAGE CODE: 32559
CHECKED: A. VALDEZ	DATE: 7/25/2025	SCALE: 5:1	SHEET # 1 OF 1
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING			