


P1: M-171
P2: M-204
P3: M-426

RE.1 2002.04.25



P1	3262	P2
1	_____	3
14	_____	7
2	_____	17
15	_____	7
3	_____	15
16	_____	7
4	_____	24
17	_____	7
5	_____	2
18	_____	7
6	_____	8
19	_____	7
23	_____	
7	_____	6
8	_____	5
11	_____	4
12	_____	20
13	_____	18
26	_____	7
SHIELD	_____	1
		SHIELD

6	MOLDED PVC BRILLIANT BLUE (MZB7036)		M304
5	UL2919 9 TWISTED PAIRS 28AWG, ALUM-MYLAR AND COPPER BRAID FOIL SHIELDING WITH DRAIN WIRE, OD 6.5, JACKET BRILLIANT BLUE (MZB7036)		M2
4	MOLDED THUMBSCREW #4-40, BRILLIANT BLUE (MZB7036)	2	M95
3	SCREW 5*47.5mm	2	M295
2	DB25 FEMALE	1	M108
1	VHDCI26 MALE	1	M110
No.	DESCRIPTION	Q'TY	Supplier
APPROVED	CompuCableUSA		Cable Length Unless Other Spec. Tolerances: 0 ~0.2M ±0.01M 0.21~1.0M ±0.02M 1.1 ~1.5M ±0.025M 1.51~2.1M ±0.03M 2.1M ↑ ±0.04M
CHECKED			
DRAWING			
ITEM NO.		DBM-CS02210	