


P1: M-171
P2: M-244

RE.1 2001.05.19



3254

P1	P2	P1	P2
1	R	7	E
14	T	8	D
2	V	11	C
15	X	12	H
3	Y	13	K
16	AA	26	B
4	U	SHIELD	A
17	W		SHIELD
5	P		
18	S		
6	F		
19	B		
22			
23			

7	MOLDED PVC BRILLIANT BLUE (MZB7036)		M304
6	UL2919 9 TWISTED PAIRS 28AWG, ALUM-MYLAR AND COPPER BRAID FOIL SHIELDING WITH DRAIN WIRE, OD 6.5, JACKET BRILLIANT BLUE (MZB7036)		M2
5	SCREW 4.5*54.9mm, MALE	1	M95
4	SCREW 4.5*55.2mm, FEMALE	1	M95
3	SCREW 5*47.5mm	2	M295
2	V.35 FEMALE	1	MB3
1	VHDCI26 MALE	1	M110
No.	DESCRIPTION	Q'TY	Supplier

APPROVED		CompuCableUSA	Cable Length Unless Other Spec. Tolerances: 0 ~0.2M ±0.01M 0.21~1.0M ±0.02M 1.1 ~1.5M ±0.025M 1.51~2.1M ±0.03M 2.1M ↑ ±0.04M
CHECKED			
DRAWING	ITEM NO. DBM-CS05210		