

Brady LED Sign Projector 60W Medium

Part Number: SP-60-UN



Mark the unmarkable with LED Sign Projectors from Brady. Ensure safety and showcase professionalism anywhere with projectors ideal for challenging and changing environments. Project a wide variety of signage onto surfaces where paint and tape can't, including those that are hot, humid, dusty, grimy, uneven and irregular. Eliminate the prep, install, waste and special training needed with disposable tapes and paints. Maintenance-free operation thanks to no fans, motors or moving parts. Designed for rugged industrial environments and is waterproof, making it safe for washdowns. Ideal for projecting medium floor signage up to 7 feet wide at up to 20 feet. Accepts E Size Sign Lenses. UL/cUL certified, IP65 rated. 35,000-hour bulb life.

FEATURES:

- Project a wide variety of signage onto surfaces where paint and tape can't, including those that are hot, humid, dusty, grimy, uneven and irregular
- Eliminate the prep, install, waste and special training needed with disposable tapes and paints
- Maintenance-free operation thanks to no fans, motors or moving parts
- Designed for rugged industrial environments and is waterproof, making it safe for washdowns
- Ideal for projecting medium floor signage up to 7 feet wide at a distance of up to 20 feet
- Accepts E Size Sign Lenses

Attribution:

Brand: Brady

Colour: Black

Country of Origin: China

Display: Assorted

RoHS Compliant: Yes

Contains CA Prop 65 Substance: No

Contains Heavy Metals: No

ECCN: EAR99

Horizontal tariff code: 9008.50.4000

Indoor or outdoor use: Indoor