

Screw connection - WP-GT PP HF M12 - 3241010

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland made from PP with metric thread, rotatable, IP54 protection

The figure shows the WP-GT PP HF M10 version

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
Custom tariff number	39174000
Country of origin	Germany

Technical data

Dimensions

Width (a)	17.5 mm
Height	38 mm
Wrench size	16.00 mm
Outside diameter	10.00 mm
Cable diameter	5.5 mm ... 5.5 mm

Ambient conditions

Ambient temperature (operation)	-10 °C ... 110 °C
Degree of protection	IP54

General

Color	gray
Type	Rotatable
	Outer thread
Components	Halogen-free
Flammability rating according to UL 94	HB
Material	PP

Standards and Regulations

Screw connection - WP-GT PP HF M12 - 3241010

Technical data

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC001178

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approvals submitted

Screw connection - WP-GT PP HF M12 - 3241010

Approvals

Approval details



Accessories

Accessories

Corrugated pipe

Protective hose - WP-SPIRAL PVC C 10 - 3240849



Protective hose, spring steel wire with PVC coating, highly stranded

Protective hose - WP-SPIRAL PU C HF 10 - 3240856



Protective hose, spring steel wire with PU coating, highly stranded
