



Cable Clamps - Fir Tree Mount - Compatible Cable Diameter 9.9 mm | 0.39 in ; Nylon 6/6

Part Number: HLCC-2BK



Hinged locking clamp securely holds corrugated or convoluted tubing and other bundles. It has an internal rib spanning the diameter of the clamp providing a tight grip and has a releasable latch that is convenient for maintenance or re-routing. The large base ensure stable mounting.

Specification:

Adjustability	Fixed
Color	Black
Standards	RMS-47
Compatible Cable Diameter Range	0.394 in
Maximum Compatible Cable Diameter	0.394 in
Minimum Operating Temperature	-40 °F
Full Material	Nylon 6/6
Material Flammability Standard	UL94 V-2
Compatible Panel Thickness Range	0.031 - 0.118 in
Maximum Compatible Panel Thickness	0.118 in
Minimum Compatible Panel Thickness	0.031 in