

WTHA1 120V

Item No: WTHA1N
Hot Air Station 900 W



KEY FEATURES

- + 900 W Hot air station for simple repair and heating tasks
- + Modern and intuitive operational concept thanks to clear menu structure
- + Reduced footprint thanks to stackability
- + Electronical controlled temperature
- + Accurate adjustment of hot air through brushless turbine
- + Up to 5 pre-sets which can be automatically run in a profile
- + Housing cover useable as storage
- + Lock function
- + Unit includes. safety rest and fixed hot air iron

Compact. Powerful. Versatile.



TECHNICAL DATA

Length	8.3 in
Dimensions L x W x H	212.0 x 172.0 x 122.0mm
Capacity (l/min)	5 - 60 l/min (20°C) 5 - 110 l/min (300°C)
Equipotential Bonding	Yes
Equipotential Bonding Socket	Via 3.5mm pawl socket on front of device
ESD Safe	Yes
Fuse	T8A
Maximum Hot Air Flow Rate l/min (Depends on Tool)	50 l/min
Number of Channels	1
Power	900 W
Temperature Accuracy °C	± 30°C
Temperature Accuracy °F	± 54°F
Temperature Accuracy for Hot Air	± 30°C, ± 54°F
Temperature Range °C	50 - 600 °C
Temperature Range °F	100 - 1000 °F
Tip Type	WT
UPC	037103308641
Voltage	120V
Weight (Catalog)	1.90 kg
Product Family	Rework, Hot Air, Desoldering Stations