



Part Number: SSA-EB1PLGR-0DECQ8

Item Detail 30 mm Mount Emergency Stop Buttons



Emergency Stop with ISD: 30 mm Mount with 40 mm Push Button

Illuminated Color: Green/Red Flashing

2 N.C. OSSD Safety Contacts, IP65

8-pin M12 QD

Specification:

Connection Type	M12
Armed Color (Solid)	Green
Actuated Color	Red - Flash
Illumination Type	Base

Button Shroud	No
ISD Connect Compatible	Yes
IP Rating	IP65
Supply Voltage	24 V dc
Item Status	RELEASED
Housing Style	Base
Device Type	Push Button
Primary Housing Material	Polycarbonate
In-Series Diagnostics	Yes
Actuation	Twist-to-Release
Connection	Integral QD
Quick Disconnect Type	M12
Feature: Illuminated	Yes
Feature: Quick Disconnect	Yes
Mounting Thread/Style	30 mm
Contact Quantity	2 NC OSSD
Contact Rating	24 V dc @ 0.1 A each
Button Diameter (mm)	40
Actuator/Button Material	Thermoplastic
Dimensions (HxWxD mm)	120 x 80
Min Operating Temperature (°C)	-25
Max Operating Temperature (°C)	50
EPLAN Status	Published
EPLAN Original Sent Date	10/18/2024