


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF EASE ELECTRONICS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF EASE ELECTRONICS IS PROHIBITED.

REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	9/10/25	CHILLY. L



MATERIAL

Keystone Jack Housing: ABS UL94V-0
 Module Clamp: ABS UL94V-0
 IDC Housing: PC UL94V-0
 IDC Contact: Phosphor Bronze C5191R-H, Nickel Plating 100u"
 PIN: Phosphor Bronze C5210-EH, t=0.35mm, 50u" Gold over Contact Pin over Nickel Plating Undercoat
 PCB Board: FR-4

Physical Characteristics

Insertion Life: 750 Mating Cycles
 Durability: 200 Termination Cycles
 Contact Compatibility: 22 ~ 24 AWG
 Operating Temperature Range: -10 °C to 60 °C
 Storage Temperature Range: -40 °C to 68 °C
 Humidity: 10% ~ 90% RH

ELECTRICAL

Insulation Resistance: 500 mΩ
 Dielectric Withstanding Voltage: 1000 V
 DC Current Rating: 1.5 Amps
 DC Resistance: 0.1 Ω
 Contact Resistance: 20 mΩ

Mounting Type

Patch Panel, Faceplates/Wall Plates, Surface Mount Boxes

UNIT: MM

Part Number Table

PART NUMBER	DESCRIPTION	DWG. NO.
RJ45-6JUD-90BK	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Black	J0137
RJ45-6JUD-90BL	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Blue	J0138
RJ45-6JUD-90GN	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Green	J0139
RJ45-6JUD-90GY	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Gray	J0140
RJ45-6JUD-90IV	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Ivory	J0141
RJ45-6JUD-90OR	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Orange	J0142
RJ45-6JUD-90RD	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Red	J0143
RJ45-6JUD-90WT	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, White	J0144
RJ45-6JUD-90YW	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Yellow	J0145

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15	APPROVALS DRAWN BY LUKE. L CHECKED BY TILLY. H APPROVED BY CHILLY. L	DATE 8/10/2025 8/10/2025 9/10/2025	 EASE Ease Electronics Co., Limited <small>Zone A, 2nd Floor, Bldg A, No.45, Qianjin 3rd Rd, Tanzhou, 528467 Zhongshan, Guangdong, China. +86-756-5888810</small>	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			PART NUMBER RJ45-6JUD-90BK
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	ID J	SERIES NO. RJ45-J
		REF	DWG. NO. J0137	SCALE: NONE CAD FILE: J0137

REV. **J**
 SHEET 1 OF 1