







THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF EASE ELECTRONICS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF EASE ELECTRONICS IS PROHIBITED.

REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	9/10/25	CHILLY. L

D

D

Available in Different Colors



Module Clamp

C

C

MATERIAL

Keystone Jack Housing: ABS UL94V-0

Module Clamp: ABS UL94V-0

IDC Housing: PC UL94V-0

IDC Contact: Phosphor Bronze C5191R-H, Nickel Plating 100u"

PIN: Phosphor Bronze C5210-EH, t=0.35mm, 50u" Gold over Contact Pin over Nickel Plating Undercoat

PCB Board: FR-4

Physical Characteristics

Insertion Life: 750 Mating Cycles

Durability: 200 Termination Cycles

Contact Compatibility: 22 ~ 24 AWG

Operating Temperature Range: -10 °C to 60 °C

Storage Temperature Range: -40 °C to 68 °C

Humidity: 10% ~ 90% RH

ELECTRICAL

Insulation Resistance: 500 mΩ

Dielectric Withstanding Voltage: 1000 V

DC Current Rating: 1.5 Amps

DC Resistance: 0.1 Ω

Contact Resistance: 20 mΩ

Mounting Type

Patch Panel, Faceplates/Wall Plates, Surface Mount Boxes

UNIT: MM

Part Number Table

PART NUMBER	DESCRIPTION	DWG. NO.
RJ45-6JUD-90BK	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Black	J0137
RJ45-6JUD-90BL	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Blue	J0138
RJ45-6JUD-90GN	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Green	J0139
RJ45-6JUD-90GY	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Gray	J0140
RJ45-6JUD-90IV	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Ivory	J0141
RJ45-6JUD-90OR	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Orange	J0142
RJ45-6JUD-90RD	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Red	J0143
RJ45-6JUD-90WT	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, White	J0144
RJ45-6JUD-90YW	Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Yellow	J0145

A

A

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15 PROJECTION 	APPROVALS	DATE	EASE Ease Electronics Co., Limited Zone A, 2nd Floor, Bldg A, No.45, Qianjin 3rd Rd, Tanzhou, 528467 Zhongshan, Guangdong, China. +86-756-58 8881 0	
	DRAWN BY LUKE. L	8/10/2025		
	CHECKED BY TILLY. H	8/10/2025	PART NUMBER RJ45-6JUD-90GY	
	APPROVED BY CHILLY. L	9/10/2025	PRODUCT DESCRIPTION Cat.6 RJ45 110 Type 90° UTP Keystone Jack, Gray	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		ID J	SERIES NO. RJ45-J	DWG. NO. J0140
COLOR VARIATIONS MAY OCCUR		REF	SCALE: NONE	CAD FILE: J0140
				SHEET 1 OF 1

B

A

6

5

4

3

2

1