

Detailed Specifications

Frame Width:	40[mm]
Frame Height:	40[mm]
Frame Depth:	10[mm]
Max. Air Flow:	4.9[CFM]
Max. Air Flow:	0.14[m3 per min]
Max. Static Pressure:	0.11[In H2O]
Max. Static Pressure:	27.5[Pa]
Fan Speed:	5500[RPM]
Noise:	21.5[dB]
Life Expectancy:	50,000 hours at 40C[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	10.2[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.04[A]
Input Power:	0.48[W]
Mass:	16[g]
Tach / Locked Rotor Output:	Locked Rotor
Status:	Active