

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	38[mm]
Max. Air Flow:	61.8[CFM]
Max. Air Flow:	1.75[m3 per min]
Max. Static Pressure:	0.46[In H2O]
Max. Static Pressure:	115[Pa]
Fan Speed:	4500[RPM]
Noise:	46[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	7[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.41[A]
Input Power:	4.9[W]
Mass:	210[g]
Tach / Locked Rotor Output:	No
Status:	Active

DC Axial Fans