

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	38[mm]
Max. Air Flow:	75.9[CFM]
Max. Air Flow:	2.15[m3 per min]
Max. Static Pressure:	0.72[In H2O]
Max. Static Pressure:	180[Pa]
Fan Speed:	5500[RPM]
Noise:	51[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	7[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.73[A]
Input Power:	8.8[W]
Mass:	210[g]
Tach / Locked Rotor Output:	No
Status:	Active