

## Detailed Specifications

<b>Frame Width:</b>	80[mm]
<b>Frame Height:</b>	80[mm]
<b>Frame Depth:</b>	38[mm]
<b>Max. Air Flow:</b>	91.8[CFM]
<b>Max. Air Flow:</b>	2.6[m3 per min]
<b>Max. Static Pressure:</b>	1.04[In H2O]
<b>Max. Static Pressure:</b>	260[Pa]
<b>Fan Speed:</b>	6500[RPM]
<b>Noise:</b>	56[dB]
<b>Life Expectancy:</b>	25 degree C 100,000 Hours[L10]
<b>Bearing Type:</b>	Ball Bearing
<b>Nominal Voltage:</b>	12[V]
<b>Operating Voltage - Lower:</b>	7[V]
<b>Operating Voltage - Upper:</b>	13.8[V]
<b>Current:</b>	1.15[A]
<b>Input Power:</b>	13.8[W]
<b>Mass:</b>	210[g]
<b>Tach / Locked Rotor Output:</b>	No
<b>Status:</b>	Active