

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	38[mm]
Max. Air Flow:	91.8[CFM]
Max. Air Flow:	2.6[m3 per min]
Max. Static Pressure:	1.04[In H2O]
Max. Static Pressure:	260[Pa]
Fan Speed:	6500[RPM]
Noise:	56[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	7[V]
Operating Voltage - Upper:	13.8[V]
Current:	1.15[A]
Input Power:	13.8[W]
Mass:	210[g]
Tach / Locked Rotor Output:	Tach Output
Status:	Active

DC Axial Fans