

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	38[mm]
Max. Air Flow:	103.8[CFM]
Max. Air Flow:	2.94[m3 per min]
Max. Static Pressure:	0.57[In H2O]
Max. Static Pressure:	142[Pa]
Fan Speed:	5000[RPM]
Noise:	52.5[dB]
Life Expectancy:	100,000 hours at 25C[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	7[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.8[A]
Input Power:	9.6[W]
Mass:	230[g]
Tach / Locked Rotor Output:	No
Status:	Active

DC Axial Fans