

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	38[mm]
Max. Air Flow:	129.95[CFM]
Max. Air Flow:	3.68[m3 per min]
Max. Static Pressure:	0.89[In H2O]
Max. Static Pressure:	222[Pa]
Fan Speed:	6200[RPM]
Noise:	59[dB]
Life Expectancy:	100,000 hours at 25C[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	7[V]
Operating Voltage - Upper:	13.8[V]
Current:	1.46[A]
Input Power:	17.52[W]
Mass:	230[g]
Tach / Locked Rotor Output:	Tach Output
Status:	Active