

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	38[mm]
Max. Air Flow:	141.2[CFM]
Max. Air Flow:	4[m3 per min]
Max. Static Pressure:	1.02[In H2O]
Max. Static Pressure:	260[Pa]
Fan Speed:	6200[RPM]
Noise:	59[dB]
Life Expectancy:	100,000 hours at 25C[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	14[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.71[A]
Input Power:	17.04[W]
Mass:	230[g]
Tach / Locked Rotor Output:	No
Status:	Active