

Detailed Specifications

Frame Width:	20[mm]
Frame Height:	50[mm]
Frame Depth:	50[mm]
Nominal Voltage:	24[V]
Max. Air Flow:	5.6[CFM]
Max. Static Pressure:	0.74[In H2O]
Speed:	5600[min-1]
Noise:	32[dB]
Life Expectancy:	25 degree C 50,000 Hours[L10]
Bearing Type:	Ball Bearing
Operating Voltage Lower:	12[V]
Operating Voltage Upper:	25.2[V]
Nominal Current:	0.08[A]
Input Power:	1.92[W]
Mass:	30[g]
Status:	Active