

Detailed Specifications

Frame Width:	150[mm]
Frame Height:	172[mm]
Frame Depth:	51[mm]
Max. Air Flow:	473[CFM]
Max. Air Flow:	13.4[m ³ per min]
Max. Static Pressure:	3.2[In H ₂ O]
Max. Static Pressure:	798[Pa]
Fan Speed:	6500[RPM]
Noise:	73[dB]
Life Expectancy:	40 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Speed Control:	PWM
Nominal Voltage:	48[V]
Operating Voltage - Lower:	36[V]
Operating Voltage - Upper:	60[V]
Current:	2.1[A]
Input Power:	100.8[W]
Mass:	800[g]
IP Rating:	Non IP model
Tach / Locked Rotor Output:	Tach Output
Status:	Active

PWM Speed Control Fans