


# Maswell 4 In 1 Combo antenna Shark Fin Shape SMA Connector 4G LTE 2x2 MIMO , GNSS and FM

AN\_GNSS\_MIMO\_FM\_072-SMA



## Mechanical dimension



# Maswell 4 In 1 Combo antenna Shark Fin Shape SMA Connector 4G LTE 2x2 MIMO , GNSS and FM

AN\_GNSS\_MIMO\_FM\_072-SMA

## Specifications

Item		Specifications	
GNSS Antenna	Dielectric Antenna	Center Frequency	1561.098MHz-1602MHz GPS/GLONASS/GAILEO/BEIDOU
		Polarization	RHCP
		Gain	2dBic (Zenith)
		V.S.W.R	<1.5
		Impedance	50Ω
	LNA	Gain	28±2dB
		Noise Figure	<2.0dB
		V.S.W.R	<2.0
		Supply Voltage	3~5V DC
		Current Consumption	<15mA
4G LTE Antenna MAIN		Frequency Range	698~960/MHz/1710~2690MHz
		V.S.W.R	<3.0
		Polarization	Linear
		Gain	3.5dBi(Zenith)
		Impedance	50Ω
4G LTE Antenna AUX		Frequency Range	698-960MHz/1710-2690MHz
		Polarization	Linear
		Gain	3.0dBi(Zenith)
		V.S.W.R	<2.0
		Impedance	50Ω

## Maswell 4 In 1 Combo antenna Shark Fin Shape SMA Connector 4G LTE 2x2 MIMO , GNSS and FM

AN\_GNSS\_MIMO\_FM\_072-SMA

### Specifications

Item	Specifications	
AM/FM Antenna	Frequency Range	520~1629KHz/76~108MHz
	V.S.WR	≤2.5
	Polarization	Linear
	Gain	FM:16±3dB:AM:5±3dB
	Impedance	50 Ω
	Supply Voltage	9~16V DC
	Current Consumption	≤60mA@12V DC
Mechanical	Cable	RG174
	Connector	GNSS: SMA Male, 4G Main/AUX:SMA Male, FM/AM: PIN
	Mounting Method	Screw
Environmental	Operating Temperature	-40°C~+85°C
	Relative Humidity	Up to 95%
	Ingress Protection	IP67 (exclude cable outlet)
	Vibration	10 to 1000Hz G=28.7m/s <sup>2</sup>
	Environmentally Friendly	ROHS Compliant





# Maswell 4 In 1 Combo antenna Shark Fin Shape SMA Connector 4G LTE 2x2 MIMO , GNSS and FM

AN\_GNSS\_MIMO\_FM\_072-SMA

## Radiation Patterns

GPS Antenna

GPS Antenna



# Maswell 4 In 1 Combo antenna Shark Fin Shape SMA Connector 4G LTE 2x2 MIMO , GNSS and FM

AN\_GNSS\_MIMO\_FM\_072-SMA

## Radiation Patterns

4G LTE Antenna

LTE Antenna

