

## Hydraulic Magnetic Supplementary Protector

**SPHM2RM0010**

**UPC:**786679754306

**Dimensions:**

- **Height:** X
- **Length:** X
- **Width:** X

**Warranties:**

- 1 year

**Specifications:**

- **Amperage Rating:** 10A
- **Number Of Poles:** Two-pole
- **Frequency Rating:** 50-60 Hz
- **Enclosure:** IP20
- **Inrush Delay:** 18 X
- **Time Delay:** Medium

**Supporting documents:**

- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - SPHM2RM0010](#)

**Certifications:**

- UL Listed
- CSA Certified
- IEC 60947-2

**Product compliance:**

- DIN VDE 0600