

Wood Moisture Meter

(Model GM610)

XE-4013-001



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Accurately measure wood moisture levels with the GM610 Digital LCD 2-Pin Wood Moisture Meter.

- The clear LCD display ensures easy-to-read results, allowing quick assessment of timber moisture content.
- Equipped with two pins for precise and reliable measurements, delivering accurate readings every time.
- Detect excessive moisture to prevent warping, cracking, and Mold growth, protecting your woodwork from damage.
- Ideal for both professional woodworkers and DIY enthusiasts, this essential tool helps maintain the quality and durability of your projects.

Specifications

Model	GM610 Wood Moisture Meter
Resolution	0.5%
Battery	2 x 1.5V AAA Battery
Humidity range	20%RH - 90%RH
Moisture Response Speed	<1s
Max. Temperature	+60°C
Min. Temperature	-10°C
Measuring range	2-40%/50%/60%/70%
Display	LCD

