

## Lollipop head digital pocket thermometer

XE-4370-001



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Get ultra-fast temperature readings with this digital thermometer in just 2 to 3 seconds. It delivers precision within  $\pm 0.1$  degrees and features a wide measurement range of  $-4^{\circ}\text{F}$  to  $482^{\circ}\text{F}$  ( $-20^{\circ}\text{C}$  to  $250^{\circ}\text{C}$ ). Perfect for checking the temperature of meats, as well as low-temperature foods like yogurt and ice cream.

- Includes screwdriver and user manual.
- Requires 1 x CR2032 button battery (included), battery cover with screw for safety.
- Magnet on the rear
- Hanging hole

## Specifications

- Temperature Range:  $-20^{\circ}\text{C}$  to  $250^{\circ}\text{C}$  ( $-4^{\circ}\text{F}$  to  $482^{\circ}\text{F}$ )
- Operational temperature range:  $-10^{\circ}\text{C}$  to  $50^{\circ}\text{C}$  ( $14^{\circ}\text{F}$  to  $122^{\circ}\text{F}$ )
- Division:  $0.1^{\circ}\text{C}$  ( $0.1^{\circ}\text{F}$ )
- LCD visible size: 28.5mm x 13.5mm
- Probe: Food grade 304 stainless steel ( $\varnothing 3.56\text{mm}$  x 120mm) Power: 1 x CR2032
- LCD display
- MAX: The reading is the maximum temperature reading since power on.
- MIN: The reading is the minimum temperature reading since power on.
- HOLD: Thermometer is under temperature reading hold mode.
- -: Minus mark
- $^{\circ}\text{C}$ : Celsius
- $^{\circ}\text{F}$ : Fahrenheit

