


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF EASE ELECTRONICS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF EASE ELECTRONICS IS PROHIBITED.

REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	9/10/25	CHILLY. L



MATERIAL
 Keystone Jack Housing: PC UL94V-0
 PIN: Phosphor Bronze C5210, t=0.3mm, 50u" Gold over Contact Pin over 60u" Nickel Plating Undercoat
 PCB Board: FR-4
 Insertion Life: 750 Mating Cycles
 Insertion and Extraction Force: ≤ 20N
 IDC Housing: PC UL94V-0
 Contact Compatibility: 22 ~ 26 AWG
 IDC Contact: Phosphor Bronze C5191, t=0.4mm, Nickel Plating 100u"
 Durability: 200 Mating Cycles

PHYSICAL CHARACTERISTICS
 Operating Temperature Range: -10 °C to 60 °C
 Storage Temperature Range: -40 °C to 68 °C
 Humidity: 10% ~ 90%

ELECTRICAL
 Insulation Resistance: 500 mΩ
 Dielectric Withstanding Voltage: 1000 V
 DC Current Rating: 1.5 Amps
 DC Resistance: 0.1 Ω
 Contact Resistance: 20 mΩ

Mounting Type
 Patch Panel, Faceplates/Wall Plates, Surface Mount Boxes

UNIT: MM

Part Number Table

PART NUMBER	DESCRIPTION	DWG. NO.
RJ45-6JUD-180BK	Cat.6 RJ45 110 Type 180° UTP Keystone Jack, Black	J0146
RJ45-6JUD-180BL	Cat.6 RJ45 110 Type 180° UTP Keystone Jack, Blue	J0147
RJ45-6JUD-180GN	Cat.6 RJ45 110 Type 180° UTP Keystone Jack, Green	J0148
RJ45-6JUD-180GY	Cat.6 RJ45 110 Type 180° UTP Keystone Jack, Gray	J0149
RJ45-6JUD-180IV	Cat.6 RJ45 110 Type 180° UTP Keystone Jack, Ivory	J0150
RJ45-6JUD-180OR	Cat.6 RJ45 110 Type 180° UTP Keystone Jack, Orange	J0151
RJ45-6JUD-180RD	Cat.6 RJ45 110 Type 180° UTP Keystone Jack, Red	J0152
RJ45-6JUD-180WT	Cat.6 RJ45 110 Type 180° UTP Keystone Jack, White	J0153
RJ45-6JUD-180YW	Cat.6 RJ45 110 Type 180° UTP Keystone Jack, Yellow	J0154

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15 PROJECTION 	APPROVALS DRAWN BY LUKE. L CHECKED BY TILLY. H APPROVED BY CHILLY. L	DATE 8/10/2025 8/10/2025 9/10/2025	 Zone A, 2nd Floor, Bldg A, No.45, Qianjin 3rd Rd, Tanzhou, 528467 Zhongshan, Guangdong, China. +86-756-5888810	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			PART NUMBER RJ45-6JUD-180WT
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION Cat.6 RJ45 110 Type 180° UTP Keystone Jack, White	ID J
	REF	SERIES NO. RJ45-J	DWG. NO. J0153	REV. J

SCALE: NONE CAD FILE: J0153 SHEET 1 OF 1