

GM1361 Temperature & Humidity Meter

XE-4012-001



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Model	GM1361 Temperature & Humidity Meter
Series	Temperature & Humidity Meter
General Description	Supplied in hard carry case
Type	K-type thermocouple temperature measuring
Accuracy of temperature	$\pm 1^{\circ}\text{C}$ or $\pm 1.8^{\circ}\text{C}$
Accuracy of humidity	$\pm 3\%$ (30-95%); $\pm 5\%$ (10-30%)
Battery	9V Battery
Dimensions	160*70*30mm
Function #1	Large LCD temperature & humidity dual display
Function #2	Data hold
Function #3	Low battery indication
Function #4	Auto /Manual power shut off
Function #5	Max/ Min function
Input Range - Type K	$-10^{\circ}\text{C} \sim 50^{\circ}\text{C}$ ($-30^{\circ}\text{C} \sim 1000^{\circ}\text{C}$ K-type)
Humidity range	5%RH \sim 98%RH
Unit selectable	$^{\circ}\text{C}$ / $^{\circ}\text{F}$ selection
Sampling rate	2.5times/sec

