

WT9055 Digital Sound Level Meter

XE-4157-001



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

The WT9055 digital sound level meter is novel, small and portable. The device is applicable for measurement of factory environments, quality control, health prevention and various environmental noise, including offices, transporting routes, stereo equipment and many more.

- Sound level measurement(dBA)
- MIN / MAX / Lock current value
- Data Hold
- LCD backlight function
- Manual / auto shutoff
- Backlight alarming

Model	WT9055
Series	Sound Level Meter
Accuracy	+/- 1.5dB
Resolution	0.1dB(A)
Battery	3 x 1.5V AAA
Dimensions	53.4mm x 31.4mm x 131.7mm
Working Temperature	0-40°C
Operating Humidity	10-80% RH
Weight	96.38g
Storage Temperature	10-60°C
Measuring range	35-130dB (A)
Important Information	Frequency response: 31.5Hz - 8KHz

