



Model DT44 Desktop RFID Reader & Tag Programmer

Specifications & Data Sheet



Model Number	Part Number	Description	Read Range
DT44	808-0044-00	Model DT44 Desktop Reader/Programmer, 4 inches square, USB, Windows based user software interface, SDK's available	Dependent Upon Tag Presented Toward Reader

Mechanical: Certifications:	Measurements:	107x107x22.5mm	4.2"x4.2"x.87"
	Material:	ABS Housing	
	Weight:	4 Ounces	114 grams
	RoHS III	REACH	CE
	FCC Part 15 & ETSI	SIL2	Free of BBP, DEHP, DBP, DIBP

RF:	Standard:	ISO 1800-6c	EPC Gen2
	Frequency:	902-928 MHz (US)	865.5-866.5 Mhz (EU)
	Power:	USB	3dBi/0-33dBm
	Security:	Password Protected	

Environmental:	Storage Temp:	-77°F to +185°F	-25°C to +85°C
	Temp, Operating:	-77°F to +185°F	-25°C to +85°C
	Life:	40 Year Shelf Life	
	Ingress Protection:	IP65	

