

Scotch® Electricians Duct Tape 2000, 2 in x 50 yds, 12 Roll Display

3M ID 80611236862, UPC 00054007434030



Specifications

Attribute Name	Value
Adhesion to Steel	20 oz/in
Applications	Electrical Maintenance
Brand	Scotch®
China RoHS - Below MCV	Yes
Color	Grey
Elongation at Break	100%
Length	50 Linear Yard
Length (Metric)	46 m
Maximum Operating Temperature (Celsius)	105 Degree Celsius
Product Type	Electricians Duct Tape
RoHS 2011/65/EU Compliant	Yes
Self Sticking/Amalgamating	No
Suitable for High Voltage	No
Таре Туре	Electrical

Tape Width (Imperial)	2 Inch
Thickness	6 mil
Thickness (Metric)	0.15 mm
Trademark	Scotch
Vulcanizing	No
Width	2 Inch
Width (Metric)	50 mm
Width (Metric)	50 mm

Details

- Easy tear
- Does not absorb water
- Clean removal (minimal residue)
- Tape measures 2 in x 50 yds x 6 mil
- Silver / Gray color
- Not recommended for sealing air ducts.
- 12 Roll Display

Scotch[®] 2000 Electrician's Duct Tape is a 6-mil water resistant duct tape with a polyvinyl chloride (PVC) backing and a rubber adhesive. Scotch 2000 is designed to be an electrician's utility tape for holding and bundling applications.

Scotch[®] 2000 Electrician's Duct Tape is a 6-mil water resistant duct tape with a polyvinyl chloride (PVC) backing and a rubber adhesive. Scotch 2000 is designed to be an electrician's utility tape for holding and bundling applications