



RADOX MFH-S B

Price upon login or request

Please login to see price

 Add to list



Product number 85003086

Identifier RADOX MFH-S B 2V1.5MM2

Variation RADOX MFH-S B 2V1.5MM2

Choose a variant

RADOX MFH-S B 2V1.5MM2

Enter your total quantity (in meters)

m

General

Specification

Specifications

Electrical data	
Voltage rating conductor - earth	600 V AC

Voltage rating conductor - conductor	1000 V AC
Max. permissible voltage rating AC conductor - earth	720 V AC
Max. permissible voltage rating AC conductor - conductor	1200 V AC
Max. permissible voltage rating DC conductor - earth	900 V DC
Max. permissible voltage rating DC conductor - conductor	1800 V DC
Test voltage AC	3500 V AC
Test voltage DC	8400 V DC

Mechanical data



Availabilities

This product is available at:

HUBER+SUHNER

Lead time 10 weeks (ex works)

Distributor

DIGIKEY

with lead time

Get in touch

Do you have questions?

We will gladly assist you. Send us a message or find your local contact:

 **Form**

To the contact form >