



RADOX 125 single core unscreened

Price upon login or request

Please login to see price

 Add to list



Product number 12535952

Identifier RXL 125 0.75MM2 WH

Variation RXL 125 0.75MM2 WH

Choose a variant

RXL 125 0.75MM2 WH

Enter your total quantity (in meters)

m

General

Specification

Documents

Specifications

Mechanical data

Temperature range (20kh)    -40 °C ... +125°C

Max. rated conductor temperature normal operation + 90 °C

EN50565/IEC60092

Short circuit temperature rating of the conductor + 250 °C

EN50565/IEC60092

Min. bending radius flexing  
Outer diameter ≤ 12mm 3 x D

Min. bending radius flexing  
Outer diameter > 12mm 4 x D



## Availabilities

This product is available at:

### HUBER+SUHNER

Lead time 9 weeks (ex works)

### Distributor

FARNELL

DIGIKEY

with lead time

with lead time

## Get in touch

Do you have questions?

We will gladly assist you. Send us a message or find your local contact:

 **Form**

[To the contact form](#) >