



RADOX 125 single core unscreened

Price upon login or request

Please login to see price

 Add to list



Product number 12536736

Identifier RXL 125 1.5MM2 YE

Variation RXL 125 1.5MM2 YE

Choose a variant

RXL 125 1.5MM2 YE

Enter your total quantity (in meters)

▲▼

 m

- General
- Specification
- Documents

Specifications

Mechanical data

Temperature range (20kh) -40 °C ... +125°C

Max. rated conductor temperature normal operation + 90 °C

EN50565/IEC60092

Short circuit temperature rating of the conductor + 250 °C

EN50565/IEC60092

Min. bending radius flexing
Outer diameter ≤ 12mm 3 x D

Min. bending radius flexing
Outer diameter > 12mm 4 x D



Availabilities

This product is available at:

HUBER+SUHNER

Lead time 9 weeks (ex works)

Distributor

[DIGIKEY](#)

with lead time

Get in touch

Do you have questions?

We will gladly assist you. Send us a message or find your local contact:

 **Form**

[To the contact form](#) >