



Master HT-1000 Butane Powered Cordless Heat Gun

Part Number: HT-1000

Master's HT-1000 Butane Powered Hot Air Gun Vs Standard Battery Powered Hot Air Gun

- Lighter Weight
- Higher Airflow
- Longer Runtime
- Only seconds to refill with butane



PERFORMANCE & DURABILITY

- **CORDLESS POWER** – Portable, lightweight, and easy to use—no cords or batteries required.
- **PORTABLE HEAT OUTPUT** – Multiple flames generate heat between 650°F-950°F.
- **FLAMELESS OPERATION** – Butane flame stays contained within the nozzle for controlled heating.
- **OUTPERFORMS BATTERY POWERED** – Outperforms battery-powered heat guns with superior runtime and lighter weight.
- **DURABLE DESIGN** – Built for long service life and consistent performance in both professional and field environments.
- **ULTRATANE® BUTANE POWERED** – Fueled by Master's premium Ultratane® butane for best performance and reliability.

USABILITY & SERVICEABILITY

- **ROTATING NOZZLE** – Adjusts 90° with five position settings to reach tight or awkward spaces.
- **SELF-IGNITING IGNITION SYSTEM** – Easy piezoelectric start eliminates the need for lighters or matches.
- **REFILLABLE FUEL TANK** – Runs up to 40 minutes on a full tank; easily refilled for continuous use.
- **INCLUDES ACCESSORY** – Comes with one shrink tube reflector for immediate out-of-box productivity.
- **VERSATILE APPLICATIONS** – Ideal for heat-activated wire terminals, shrinking tubing, bending laminates, thawing metal pipes, loosening rusted parts, and more.

In-The-Box

- (1) HT-1000 Butane Powered Cordless Heat Gun
- (1) Heat Shrink Attachment

HT-1000 Cordless Heat Gun Specifications

Temp at Nozzle: 650F to 950F (343C to 510C)

Power: 366 watts max

Tank Capacity: 33.38ml (1.13 fl oz, 20 grams)

Approx Run Time on Full Tank: 40 mins at high setting

Dimensions: 7.1"L x 7.6"H x 1.2"W

Tool Weight: 20.6 oz

Shipped Empty (purchase butane fuel separately)