


APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/20/17	



SPECIFICATIONS:
Material:
Insulator: PBT
Insulator color: Black
Contacts: Copper, Nickel plated
Electrical:
Voltage & Current rating : 30 VDC, 0.5 A
Contact resistance: 30 mohms max
Insulation resistance: 100 Mohms min
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
Operating temperature: -25°C to +70°C
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	HR	4/20/17
CHECKED	MY	4/20/17
APPROVED		

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
AUDIO STEREO PLUG, 3.5MM, STRAIGHT

SIZE X	PART NO. ASP-3.5-S3-24.2	REV. -
------------------	------------------------------------	------------------

REF: S00288T	SCALE: NTS	SHEET 1 OF 1
--------------	------------	--------------