

Power Supply Replacement Cords

3-Conductor Grounded • Types SJ, SJOW and SJOOW • 60° C • 300 Volts



CATALOG NUMBER	CORD TYPE	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			NEMA CONFIG.	PLUG CONFIG.	PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
						VOLTS	AMPS	WATTS						
02685.70.01	SJOOW	3	18	8	Black	125	10	1250	5-15P	Straight	25	0.6	14	079407026852
02686.70.01	SJOW	3	16	8	Black	125	13	1625	5-15P	Straight	35	0.7	24	079407026869
04932.70.01	SJ	3	16	12	Black	125	13	1625	5-15P	Straight	50	0.8	40	079407049325
04929.70.01	SJ	3	16	9	Black	125	13	1625	5-15P	Straight	50	0.6	30	079407049295
04926.70.01	SJ	3	16	6	Black	125	13	1625	5-15P	Straight	50	0.6	28	079407049264

Product Construction:

Conductor:

- 18 AWG or 16 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded EPDM

Jacket:

- CPE; black

Applications:

- For replacement use

Features:

- For replacement use
- Straight plug

Industry Approvals:

- UL Listed
- CSA

Power Supply Replacement Cords

2 and 3 Conductor • Types SJT and ST • 60° C • 300 Volts and 600 Volts



CATALOG NUMBER	CORD TYPE	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			NEMA CONFIG.	PLUG CONFIG.	PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
						VOLTS	AMPS	WATTS						
300 Volt														
02523.73.01	SJT	3	18	3	Black	125	10	1250	5-15P	Straight	50	0.2	12	079407025237
01364.70.01	SJT	3	18	8'2"	Black	125	10	1250	5-15P	Straight	50	0.5	25	079407213641
02524.73.01	SJT	3	16	3	Black	125	13	1625	5-15P	Straight	50	0.3	14	079407025244
02547.70.01	SJT	3	16	6	Black	125	13	1625	5-15P	Straight	25	0.5	13	079407018444
01513.70.01	SJT	3	16	8'2"	Black	125	13	1625	5-15P	Straight	45	0.7	32	079407315130
04949.60.10	SJT	3	16	9	Gray	125	13	1625	5-15P	Straight	50	0.7	35	079407049493
01614.70.01	SJT	3	16	12	Black	125	13	1625	5-15P	Straight	50	0.9	44	079407016143
01278.70.01	SJT	2	16	8	Black	125	13	1625	1-15P	Straight	30	0.5	14	079407012787
01950.70.01	SJT	3	14	8	Black	125	15	1875	5-15P	Straight	50	0.8	41	079407019502
600 Volt														
01951.70.01	ST	3	12	8	Black	125	15	1875	5-15P	Straight	25	1.8	45	079407719518

With Switch

	CORD TYPE	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			NEMA CONFIG.	PLUG CONFIG.	SWITCH SPEED	PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
01732.70.01	SJT	3	18	8	Black	125	10	1250	5-15P	Straight	1 Speed (On/Off)	25	0.7	18	079407017324
02053.70.01	SJT	3	18	12	Black	125	10	1250	5-15P	Straight	1 Speed (On/Off)	15	0.8	12	079407020539

With Strain Relief

	CORD TYPE	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			NEMA CONFIG.	PLUG CONFIG.	STRAIN RELIEF	PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
02548.70.01	SJT	3	16	6	Black	125	13	1625	5-15P	Straight	7" From Free End	25	0.5	13	079407025480

With Receptacle Only

	CORD TYPE	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			NEMA CONFIG.	RECEPTACLE CONFIG.	PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
04530.73.01	SJT	3	16	3	Black	125	13	1625	5-15R	Straight	50	0.2	9	079407045303

Product Construction:

Conductor:

- 18 AWG through 12 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; black or gray

Applications:

- For replacement use

Features:

- Straight plug
- Conductor stripped 5/8"
- Jacket removed 11/2"

Industry Approvals:

- UL Listed
- CSA

