

RAFIX 22 QR - Emergency stop pushbutton

1.30.243.501/0300

Included: Ring nut with claw.



Switching position indication: In the non-operated condition, a green ring is visible on the side.

| General information | |
|---|--|
| Actuator | mushroom |
| Color of mushroom | opaque red |
| Form of collar | round |
| | |
| Dimensions | |
| Dimensions of collar | ø 29.8 mm |
| Overall height | 40.1 mm |
| Mounting depth with contact block without cable | 56.4 mm |
| Mounting hole | ø 22.3 mm |
| Mounting grid | - mm |
| Mechanical design | |
| Mounting | ring nut |
| Contact function | latching |
| Illuminability | no |
| Reset | by clockwise rotation |
| Lock type | - |
| Mechanical characteristics | |
| Operating force max. | approx. 5 N for 1 switching element |
| Robustness max. | 100 N |
| Robustness | acc. to IEC 60947-5-5 |
| Other specifications | |
| Operating life (operations) | 100,000 cycle |
| Degree of protection from front side | IP65 (DIN EN 60529) |
| Ambient temp. operating min. | -25 °C |
| Ambient temp. operating max. | +70 °C |
| Storage temperature min. | -40 °C |
| Storage temperature max. | +80 °C |
| Environmental restistance | acc. to IEC 60068-2-14, -30, -33 and -78 |
| ROHS compliant | yes |
| REACH compliant | yes |
| · | |



Panel cut-out to IEC 60947-5-1



