



## **LPMM-S5-M Cable Tie Mount, Natural, PA 6.6, Screw, 0.4x0.32", PK1000**

### **LPMM-S5-M**

Panduit LPMM-S5-M Screw Applied Cable Tie Mounts have a low profile design that keeps the cable bundles secure and close to the surface. Installs with a #5 (M3) screw and with miniature cable ties. Made of Nylon 6.6, are natural in color and come in packages of 1000

### **Specifications**

|                                    |   |
|------------------------------------|---|
| Material Description               | Nylon 6.6   |
| Product Type                       | Cable Tie Mount   |
| Application                        | Low Profile Mount Designed to Secure Wire Bundles Where Space is Limited. |
| Color                              | Natural   |
| Environment                        | Indoor  |
| Material                           | Nylon 6.6   |
| Maximum Operating Temperature (°C) | 85  |
| Maximum Operating Temperature (°F) | 185   |
| Minimum Operating Temperature (°C) | -60   |
| Minimum Operating Temperature (°F) | -76   |
| Mount Method                       | Screw-On  |
| Mounting Hole Thread Size          | #5  |
| Overall Length (In.)               | 0.4   |
| Overall Length (mm)                | 10.2  |
| Overall Width (In.)                | 0.32  |
| Overall Width (mm)                 | 50.3  |
| Overall Height (mm)                | 2.5   |
| Standards Met                      | CE Compliant, RoHS Compliant  |
| For Use With                       | Miniature Cross-Section Ties  |

### **Packaging Detail**

|                       |             |
|-----------------------|-------------|
| UPC                   | 07498358053 |
| Std. Pkg. Qty.        | 1000        |
| Std. Pkg. Volume (cf) | 0.0284      |
| Std. Ctn. Qty.        | 10000       |
| Std. Ctn. Volume (cf) | 0.2839      |