



## LPMM-S5-M20 Cable Tie Mount

### LPMM-S5-M20

The low profile cable tie mount in black is applied with a #5 (M3) screw. It is made of nylon 6.6, which increases mechanical strength, heat and wear resistance, and stiffness. It is used with cable ties M, is designed for indoor environments, and comes in packages of 1000.

### Specifications

Material Description	Nylon 6.6
Product Type	Cable Tie Mount
Application	Low Profile Mount Designed to Secure Wire Bundles Where Space is Limited.
Color	Black
Flammability Rating	UL94V-2
Environment	Indoor
Material	Nylon 6.6
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Minimum Loop Tensile Strength (N)	80
Minimum Loop Tensile Strength (lb)	18
Mount Method	Screw-On
Mounting Hole Thread Size	#5
Overall Length (In.)	0.1
Overall Length (mm)	2.5
Overall Width (In.)	0.32
Overall Width (mm)	8.1
Overall Height (In.)	0.4
Overall Height (mm)	10.2
Standards Met	cULus 52275 Type 2, 21, CE Compliant, RoHS Compliant
For Use With	Miniature Cross-section Cable ties

**Packaging Detail**

UPC	07498339112
Std. Pkg. Qty.	1000
Std. Pkg. Volume (cf)	0.0284
Std. Ctn. Qty.	10000
Std. Ctn. Volume (cf)	0.2839