

# GCQ0335C1H100JB01#

Note: If you have not downloaded this document from our official website, please note that the information provided may not be the most current.  
 Please download the latest datasheet of GCQ0335C1H100JB01# from the official website of Murata  
<http://www.murata.com/en-us/products/productdetail?partno=GCQ0335C1H100JB01%23>

"#"at the end indicates the package specification code.



## < List of part numbers with package codes >

GCQ0335C1H100JB01D

GCQ0335C1H100JB01W

GCQ0335C1H100JB01J

GCQ0335C1H100JB01V

## Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Automotive powertrain/safety equipment, Automotive infotainment/comfort equipment, Medical equipment [IHTF A/B/C] except for implant equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.


## References

Packaging	Specifications	Standard Packing Quantity
D	ø180mm Reel Paper Tape	15000
W	ø180mm Reel W8P1 Paper Tape	30000
J	ø330mm Reel Paper Tape	50000
V	ø330mm Reel W8P1 Paper Tape	150000

## Mass (typ.)

1 piece	0.33mg
---------	--------

## Appearance & Shape



### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.  
 2. This datasheet has only typical specifications because there is no space for detailed specifications.  
 Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GCQ0335C1H100JB01#

"#"at the end indicates the package specification code.

## Specifications

Length	0.6±0.03mm
Width	0.3±0.03mm
Thickness	0.3±0.03mm
Capacitance	10pF ±5%
Distance between external terminals g	0.2mm min.
External terminal size e	0.1 to 0.25mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	50Vdc
Size code in inch(mm)	0201 (0603M)
TC	0±30ppm/°C
Temperature characteristics (complied standard)	C0G(EIA)
Temperature range of temperature characteristics	25°C to 125°C

**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GCQ0335C1H100JB01#





Note: If you have not downloaded this document from our official website, please note that the information provided may not be the most current.  
 Please download the latest datasheet of GCQ0335C1H100JB01# from the official website of Murata  
<http://www.murata.com/en-us/products/productdetail?partno=GCQ0335C1H100JB01%23>

"#"at the end indicates the package specification code.



## Characteristic Data

The charts below may show another part number which shares its characteristics.





### Attention

- This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GCQ0335C1H100JB01#

"#"at the end indicates the package specification code.

**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.