

Protective Glass PG08

Part number	4401-304-005-00		
Wavelength	λ	(nm)	532
LIDT coating @ 532nm, 6ns, 10.000 pulses, 100Hz		(J/cm ²)	10
Coating Diameter	$\varnothing_E$	(mm)	72.0
Diameter	$\varnothing$	(mm)	75.0
Thickness	d	(mm)	1.6

