

Protective Glass PG13

Part number	4401-496-005-01		
Wavelength	λ	(nm)	515 – 540nm, low absorption
LIDT coating @ 532nm, 8ns, 10.000 pulses, 100Hz		(J/cm ²)	20
LIDT coating @ 515nm, 204fs, 1.000 pulses, 50kHz		(J/cm ²)	0.6
Coating Diameter	$\varnothing_E$	(mm)	109.0
Diameter	$\varnothing$	(mm)	113.0
Thickness	d	(mm)	3.0

