

Protective Glass PG14

Part number	4401-499-005-00		
Wavelength	λ	(nm)	1030 – 1080nm, low absorption
LIDT coating @ 1064nm, 12ns, 1.000 pulses, 100Hz		(J/cm ²)	40
LIDT coating @ 1030nm, 291fs, 1.000 pulses, 5kHz		(J/cm ²)	0.9
Coating Diameter	$\varnothing_E$	(mm)	109.0
Diameter	$\varnothing$	(mm)	113.0
Thickness	d	(mm)	3.0

