

Protective Glass PG22

Part number	4401-551-016-00		
Wavelength	λ	(nm)	1030 – 1080nm, low absorption
LIDT coating @ 1064nm, 12ns, 1.000 pulses, 100Hz		(J/cm ²)	40
LIDT coating @ 1030nm, 291fs, 1.000 pulses, 5kHz		(J/cm ²)	0.9
Coating Diameter	$\varnothing_E$	(mm)	66.3
Diameter	$\varnothing$	(mm)	75.0
Thickness	d	(mm)	1.5

